


Product data sheet

Specifications



Glazed door for PLM64T with locking

NSYDPLM64TG

Main

Range	Thalassa
Accessory / Separate Part Category	Enclosure accessory
Product Or Component Type	Door
Application	Multi-purpose
For Enclosure Nominal Dimensions	-
Mounting Location	Front
Range Compatibility	Thalassa Thalassa PLM
Device Composition	1 door
Quantity Per Set	Set of 1

Complementary

Material	Door: polyester reinforced with fibreglass
Colour	Door: grey (RAL 7035)
Door Type	Glazed
Door Opening Side	Right (180 °) Left
Maximum Load	50 kg/m²
Height	647 mm
Width	436 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.0 cm
Package 1 Width	46.0 cm
Package 1 Length	67.0 cm
Package 1 Weight	3.803 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information