

# Product data sheet

Specifications



## Door for wall mounting enclosure Spacial S3HD - 1000x600 mm

NSYDS3HD106

### Main

Range	Spacial
Accessory / Separate Part Category	Enclosure accessory
Product Or Component Type	Door
Application	Heavy duty
For Enclosure Nominal Dimensions	- H: 1000 mm W: 600 mm
Mounting Location	Front
Range Compatibility	Spacial Spacial S3HD compact enclosure
Device Composition	1 door 3 hinges 1 lock with 3 mm double bar insert
Quantity Per Set	Set of 1

### Complementary

Material	Door: steel with anti-corrosive coating
Colour	Grey (RAL 7035)
Surface Finish	Polyester powder
Lock Type	Lock 3 mm double bar
Number Of Locks	1
Door Type	Plain
Door Opening Side	Reversible (120 °)
Maximum Load	200 kg
Height	1000 mm nominal:
Width	600 mm nominal:
Thickness	1.5 mm
Net Weight	7.425 kg

### Environment

Ik Degree Of Protection	IK10 conforming to IEC 62262
Environmental Characteristic	Corrosion resistance C4H conforming to ISO 12944: 1999 UV resistant conforming to IEC 62208

### Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
Package 1 Height	5.0 cm
Package 1 Width	61.0 cm
Package 1 Length	101.0 cm
Package 1 Weight	7.425 kg
Unit Type Of Package 2	PAM
Number Of Units In Package 2	10
Package 2 Height	68.0 cm
Package 2 Width	100.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	117.34 kg