

# Product data sheet

Specifications



## Door for wall mounting enclosure Spacial S3HD - 400x300 mm

NSYDS3HD43

### Main

Range	Spacial
Accessory / Separate Part Category	Enclosure accessory
Product Or Component Type	Door
Application	Heavy duty
For Enclosure Nominal Dimensions	- H: 400 mm W: 300 mm
Mounting Location	Front
Range Compatibility	Spacial Spacial S3HD compact enclosure
Device Composition	1 door 2 hinges 1 lock with 3 mm double bar insert
Quantity Per Set	Set of 1

### Complementary

Material	Door: steel with anti-corrosive coating
Colour	Grey (RAL 7035)
Surface Finish	Polyester powder
Lock Type	Lock 3 mm double bar
Number Of Locks	1
Door Type	Plain
Door Opening Side	Reversible (120 °)
Maximum Load	200 kg
Height	400 mm nominal:
Width	300 mm nominal:
Thickness	1.5 mm
Net Weight	1.485 kg

### Environment

Ik Degree Of Protection	IK10 conforming to IEC 62262
Environmental Characteristic	Corrosion resistance C4H conforming to ISO 12944: 1999 UV resistant conforming to IEC 62208

### Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
Package 1 Height	5.0 cm
Package 1 Width	31.0 cm
Package 1 Length	41.0 cm
Package 1 Weight	1.485 kg
Unit Type Of Package 2	PAM
Number Of Units In Package 2	20
Package 2 Height	45.0 cm
Package 2 Width	100.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	49.24 kg

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

 Mercury Free	
 Rohs Exemption Information	<a href="#">Yes</a>
Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information