

# Product data sheet

Specifications

## Cost-effective LED Lamps - 24/48 V DC - 5W



NSYLAMT5LD1VDC

### Main

Range Of Product	Lighting and power sockets
Accessory / Separate Part Category	Lighting accessory
Product Or Component Type	Lamp
Device Application	Multi-purpose
Device Composition	1 lamp 1 fixing elements 2 cable
Power Factor	1

### Complementary

Outlet Standard Deviation	Without socket
Rated Lamp Wattage	5 W
[Ue] Rated Operational Voltage	24/48 V DC
Bulb Base	Integral LED
Bulb Type	LED
Control Type	Built-it switch
Luminous Flux	470 lm
Colour Temperature	4000 K
Service Life In Hours	25000 h
Electrical Connection	Cable quick connector 3 m supplied Cable quick connector 1 m supplied
Mounting Support	Metal parts Cross rails
Fixing Mode	Screws Magnetic fixing
Range Compatibility	Spacial Thalassa
Length	310 mm
Height	30.5 mm
Colour	Aluminium

### Environment

Ip Degree Of Protection	IP20 conforming to IEC 60529
Electrical Insulation Class	Class I

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	IEC 60598
Ambient Air Temperature For Operation	-10...60 °C
Ambient Air Temperature For Storage	-16...65 °C

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.9 cm
Package 1 Width	5.4 cm
Package 1 Length	35.0 cm
Package 1 Weight	200.0 g

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	<a href="#">End of Life Information</a>