

Product data sheet

Specifications



PLD - Floor standing encl.polyester w/plinth open bottom 850x1115x320 IP43 DIN2

NSYPLD8122C

ⓘ Discontinued

Main

Range	Thalassa
Category	Enclosure
Version	PLD
Enclosure Type	Distribution enclosure DIN enclosure
Nominal Height	850 mm
Nominal Width	1115 mm
Nominal Depth	320 mm
Enclosure Mounting	Floor-standing
Product Compatibility	Fuse 2

Complementary

Device Composition	1 top part 1 bottom part 2 side part 1 rear panel 2 door 2 key lock 1 central upright
Body Type	Sealed top and open bottom part assembled with side parts
Door Type	Plain front
Number Of Doors	2 door(s)
Door Opening Side	Right and left (180 °)
Lock Type	Key lock
Key Number	1242 E
Accessibility For Operation	Front Bottom
Removable Parts	Door by hinges
Material	Polyester reinforced with fibreglass
Colour	Grey (RAL 7032)

Environment

Standards	IEC 62208
Ip Degree Of Protection	IP43 conforming to IEC 60529 (plinth type open bottom) IP54 conforming to IEC 60529 (with additional sealing kit)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ik Degree Of Protection	IK10 conforming to IEC 62262 (plain door)
Fire Resistance	960 °C conforming to IEC 62208
Ambient Air Temperature For Storage	-35...90 °C