

# Product data sheet

Specifications



## PLD - Floor standing encl.polyester w/plinth open bottom 850x465x320 IP43 DIN00

NSYPLD8500

ⓘ Discontinued

### Main

Range	Thalassa
Category	Enclosure
Version	PLD
Enclosure Type	DIN enclosure Distribution enclosure
Nominal Height	850 mm
Nominal Width	465 mm
Nominal Depth	320 mm
Enclosure Mounting	Floor-standing
Product Compatibility	Fuse 00

### Complementary

Device Composition	1 top part 1 bottom part 2 side part 1 rear panel 1 key lock 1 door
Body Type	Sealed top and open bottom part assembled with side parts
Door Type	Plain front
Number Of Doors	1 door(s)
Door Opening Side	Reversible (180 °)
Lock Type	Key lock
Key Number	1242 E
Accessibility For Operation	Bottom Front
Removable Parts	Door by hinges
Material	Polyester reinforced with fibreglass
Colour	Grey (RAL 7032)

### Environment

Standards	IEC 62208
Ip Degree Of Protection	IP43 conforming to IEC 60529 (plinth type open bottom) IP54 conforming to IEC 60529 (with additional sealing kit)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

<b>Ik Degree Of Protection</b>	IK10 conforming to IEC 62262 (plain door)
<b>Fire Resistance</b>	960 °C conforming to IEC 62208
<b>Ambient Air Temperature For Storage</b>	-35...90 °C