

Product data sheet

Specifications



Spacial SF 19" fixed rack - 2200 mm

NSYRCK47

Main

Range	Spacial
Accessory / Separate Part Category	Mounting accessory
Product Or Component Type	19" rack
Application	Electronic application
For Enclosure Nominal Dimensions	- H: 2200 mm
Rack Type	Fixed
Mounting Location	On structure of enclosure
Mounting Support	19" fixed support bracket
Range Compatibility	Spacial Spacial SF Spacial Spacial SM
Device Composition	fixing elements 2 upright
Quantity Per Set	Set of 1
Number Of Units 19"	47

Complementary

Material	Steel
Enclosure/Cubicle Description	Floor-standing enclosure
Surface Finish	Zinc coated
Fixing Mode	By fixing element
Adjustment	Adjustable in depth every 25 mm
Permanent Permissible Load	400 kg
Height	2200 mm
Depth	45 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	210.0 cm
Package 1 Width	11.0 cm
Package 1 Length	4.5 cm
Package 1 Weight	7.2 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations