

Product data sheet

Specifications



Wall mounted steel enclosure,
Spacial S3DC, plain door, without
plain chasis, 1000x1000x300mm,
IP66, IK10

NSYS3DC101030

Main

| | |
|-----------------------------|----------------------------|
| Range | Spacial |
| Product Name | Spacial S3DC |
| Application | Multi-purpose |
| Category | Compact enclosure |
| Enclosure Nominal Height | 1000 mm |
| Enclosure Nominal Width | 1000 mm |
| Enclosure Nominal Depth | 300 mm |
| Door Type | Plain |
| Mounting Plate Description | Without mounting plate |
| Type Of Gland Plate | Without gland plate |
| Installation Accessory Type | Wall-mounting |
| Device Composition | 1 body 1 door 1 lock |

Complementary

| | |
|-----------------------------|---|
| Body Type | Gutter-shaped front profile double sheet thickness Single piece body |
| Number Of Doors | Front face: 1 door(s) |
| Door Opening Side | Reversible (120 °) |
| Lock Type | 3 points lock, screw driver insert |
| Accessibility For Operation | Front |
| Removable Parts | Door by hinges |
| Material | Steel |
| Surface Finish | Epoxy-polyester powder |
| Colour | Grey (RAL 7035) |
| Standards | IEC 62208 |
| Product Certifications | UL |
| Net Weight | 45 kg |

Environment

| | |
|---------------------------|------------------------------|
| Nema Degree Of Protection | NEMA 4X/13 |
| Ik Degree Of Protection | IK10 conforming to IEC 62262 |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|-------------------------|------------------------------|
| Ip Degree Of Protection | IP66 conforming to IEC 60529 |
|-------------------------|------------------------------|

Packing Units

| | |
|------------------------------|----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 35.0 cm |
| Package 1 Width | 103.0 cm |
| Package 1 Length | 110.0 cm |
| Package 1 Weight | 45.0 kg |
| Unit Type Of Package 2 | P12 |
| Number Of Units In Package 2 | 2 |
| Package 2 Height | 117.0 cm |
| Package 2 Width | 80.0 cm |
| Package 2 Length | 120.0 cm |
| Package 2 Weight | 100.0 kg |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

| | |
|--------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |