

Product data sheet

Specifications



Wall mounted enclosure, Spacial S3X, stainless steel 304L, plain door, 400x300x200mm, IP66

NSYS3X4320

Main

| | |
|----------------------|----------------------------------|
| Range | Spacial |
| Product Name | Spacial S3X |
| Enclosure Type | Multi-purpose |
| Category | Compact enclosure |
| Nominal Height | 400 mm |
| Nominal Width | 300 mm |
| Nominal Depth | 200 mm |
| Product Installation | Wall-mounting |
| Device Composition | 1 body 1 lock: door 1 door |

Complementary

| | |
|-----------------------------|--|
| Body Type | Single piece body, cross-shaped structure Gutter shaped front rail |
| Door Type | Plain |
| Number Of Doors | Front face: 1 door(s) |
| Door Opening Side | Reversible (120 °) |
| Lock Type | 3 mm double-bar lock |
| Mounting Plate Description | Without mounting plate |
| Type Of Gland Plate | Without gland plate |
| Accessibility For Operation | Front |
| Removable Parts | Door by hinges |
| Material | Body and door: stainless steel 304L Lock: zamak Hinge: stainless steel |
| Surface Finish | Body and door: Scotch-Brite® brushed Lock: chromium plated |
| Net Weight | 5.468 kg |

Environment

| | |
|-------------------------|------------------------------|
| Standards | IEC 62208 |
| Product Certifications | UL 508 type A CAN/CSA 22 |
| Ip Degree Of Protection | IP66 conforming to IEC 60529 |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|-------------------------------------|-------------------------------|
| Ik Degree Of Protection | IK10 conforming to IEC 62262 |
| Environmental Characteristic | Corrosive Specific hygiene |

Packing Units

| | |
|-------------------------------------|----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 21.5 cm |
| Package 1 Width | 31.0 cm |
| Package 1 Length | 41.5 cm |
| Package 1 Weight | 5.468 kg |
| Unit Type Of Package 2 | PAM |
| Number Of Units In Package 2 | 64 |
| Package 2 Height | 180.0 cm |
| Package 2 Width | 100.0 cm |
| Package 2 Length | 120.0 cm |
| Package 2 Weight | 378.6 kg |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty | 18 months |
|-----------------|-----------|

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

| | |
|--------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |