

Product data sheet

Specifications



Metal industrial box plain door H300xW800xD120 IP66 IK10 RAL 7035

NSYSBM308012

Main

Range	Spacial
Product Name	Spacial SBM
Device Application	Multi-purpose
Category	Industrial box
Device Short Name	SBM
Enclosure Type	Flat face box
Enclosure Nominal Height	300 mm
Enclosure Nominal Width	800 mm
Enclosure Nominal Depth	120 mm
Enclosure Mounting	Wall mounted
Device Composition	1 cover 1 body 6 cover screw
Body Type	Single piece body folded and welded
Type Of Front Cover	Plain door
Cover Fixing	Half turn metal screw
Lock Type	Captive screw PZ2 outside sealed area
Removable Parts	Cover by captive screws

Complementary

Material	Sheet steel
Surface Finish	Polyester powder
Colour	Grey (RAL 7035)
Standards	IEC 62208
Product Certifications	LR DNV-GL UL BV
Ip Degree Of Protection	IP66 conforming to IEC 60529
Ik Degree Of Protection	IK10 conforming to IEC 62262
Ambient Air Temperature For Storage	-35...60 °C
Operating Temperature	-35...80 °C
Net Weight	8.73 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	14.5 cm
Package 1 Width	32.5 cm
Package 1 Length	82.5 cm
Package 1 Weight	8.73 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	12
Package 2 Height	90.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	118.0 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations