

Product data sheet

Specifications



Spacial SD Compact control desk with rear panel - H1000xW1200xD597 - IP55

NSYSD12R

Main

Range	Spacial
Product Name	Spacial SD
Enclosure Type	Multi-purpose
Category	Monobloc control desk with rear panel
Nominal Height	1000 mm
Nominal Width	1200 mm
Nominal Depth	597 mm
Product Installation	Floor-standing
Device Composition	1 structure 2 lock: door 4 adjustment rail 1 cable gland plate 2 pneumatic stay: desk lid 2 door 1 rear panel 5 top plate: on top of control desk

Complementary

Body Type	Single piece structure folded and welded
Door Type	Plain
Number Of Doors	Front: 2 door(s)
Door Opening Side	Reversible 120 ° door
Lock Type	2 points lock, 3 mm double-bar
Mounting Plate Description	Without mounting plate
Type Of Gland Plate	1 entry plate
Accessibility For Operation	Rear Front
Removable Parts	Door by hinges Desk lid by hinges Cable gland plate by clipping screws Blanking covers by screws Rear panel by screws
Material	Body: steel
Surface Finish	Epoxy-polyester powder
Thickness	1.5 mm
Colour	Grey (RAL 7035)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Standards	IEC 62208
Ip Degree Of Protection	IP55 conforming to IEC 60529
Ik Degree Of Protection	IK10 conforming to IEC 62262

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	100.0 cm
Package 1 Width	120.0 cm
Package 1 Length	130.0 cm
Package 1 Weight	113.0 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations