

# Product data sheet

Specifications



Modular stainless console 304L,  
Scotch Brite® finishing, W400xD200  
mm.

NSYSDCX42

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

## Main

Range	Spacial
Accessory / Separate Part Category	Interface accessory
Product Or Component Type	Modular consoles
Anwendung	Multi-purpose
Nennmaße Des Gehäuses	-
Mounting Location	Top of control desk
Mounting Support	Direct fixing
Range Compatibility	Spacial Spacial SDX
Device Composition	1 door 1 body 1 lock 1 door retainer
Quantity Per Set	Set of 1

## Complementary

Material	Stainless steel 304L
Surface Finish	Scotch-Brite® brushed
Lock Type	Lock 3 mm double bar
Fixing Mode	By fixing element
Operating Angle	75 °
Height	483 mm
Width	Nominal: 400 mm
Depth	Nominal : 200 mm Maximum : 262 mm

## Environment

Ip Degree Of Protection	IP55
Ik Degree Of Protection	IK10
Net Weight	12 kg

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	28.0 cm
Package 1 Width	41.5 cm
Package 1 Length	51.0 cm
Package 1 Weight	12.0 kg
Unit Type Of Package 2	PAM
Number Of Units In Package 2	10
Package 2 Height	93.0 cm
Package 2 Width	100.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	133.0 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>