

Product data sheet

Specifications



Lifting bar, PanelSeT SFN, PanelSet SF, L1800mm , steel , set of 2

NSYSFTB18

Main

Area	PanelSeT
Category	Lifting accessory
Product Or Component Type	Lifting bar
Application	Multi-purpose
Mounting Location	Enclosure top
Mounting Support	Directly in the axis of the uprights
Range Compatibility	PanelSeT PanelSeT SF PanelSeT PanelSeT SFHD PanelSeT PanelSeT SFM
Device Composition	2 lifting bars fixing elements
Quantity Per Set	Set of 1

Complementary

Material	Steel
Surface Finish	Zinc coated
Fixing Mode	By screws - screw type M12
Permanent Permissible Load	3000 kg
Length	Nominal: 1800 mm Real: 1795 mm
Height	60 mm
Depth	60 mm
Diameter	32 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.5 cm
Package 1 Width	12.0 cm
Package 1 Length	229.0 cm
Package 1 Weight	30.3 kg

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability





Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation		China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)