


# Product data sheet

Specifications



## Spacial SF top busbar chamber - IP55 - 300x300x600 mm

NSYTBC336

### Main

Range	Spacial
Accessory / Separate Part Category	Power distribution
Product Or Component Type	Top busbar chamber
Application	Multi-purpose
Range Compatibility	Spacial Spacial SF
Nominal Dimensions Of The Housing	-
Mounting Location	On top of enclosure
Device Composition	1 busbar chamber 1 sealing gasket 2 front panel
Quantity Per Set	Set of 1
Material	Steel

### Complementary

Colour	Grey (RAL 7035)
Surface Finish	Epoxy-polyester powder
Height	301 mm
Width	300 mm
Depth	600 mm
Ip Degree Of Protection	IP55 conforming to IEC 60529

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	14.0 cm
Package 1 Width	32.0 cm
Package 1 Length	62.0 cm
Package 1 Weight	15.8 kg
Unit Type Of Package 2	PAM
Number Of Units In Package 2	12
Package 2 Height	85.0 cm
Package 2 Width	100.0 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Length	120.0 cm
Package 2 Weight	229.0 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance



Mercury Free



RoHS Exemption Information

Yes

## Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu RoHS Directive

Pro-active compliance (Product out of EU RoHS legal scope)

China RoHS Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

No need of specific recycling operations