

# Product data sheet

Specifications



Plug-in bridge, Linergy TR, 10 points, for 2.5mm<sup>2</sup> terminal blocks, red, 10 way, set of 10

NSYTRAL210

## Main

|                                    |   |
|------------------------------------|---|
| Range                              | Linergy   |
| Product Name                       | Linergy TR  |
| Product Or Component Type          | Plug-in bridge  |
| Device Short Name                  | TRA   |
| Accessory / Separate Part Category | Connection accessory  |
| Product Compatibility              | TRV screw terminal terminal block<br>TRP push-in terminal block<br>TRR spring terminal terminal block<br>TRH IDC terminal block |
| Number Of Ways                     | 10 ways   |

## Complementary

|                             |                       |
|-----------------------------|-----------------------|
| Cable Cross Section         | 2.5 mm <sup>2</sup>   |
| Number Of Connections       | 2<br>3<br>4           |
| Number Of Measurement Input | 3<br>1<br>2<br>4<br>6 |
| Quantity Per Set            | Set of 10             |
| Net Weight                  | 9 g                   |
| Colour                      | Red                   |

## Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type Of Package 1       | PCE     |
| Number Of Units In Package 1 | 1       |
| Package 1 Height             | 5.0 cm  |
| Package 1 Width              | 15.0 cm |
| Package 1 Length             | 17.0 cm |
| Package 1 Weight             | 8.0 g   |
| Unit Type Of Package 2       | BAG     |
| Number Of Units In Package 2 | 10      |
| Package 2 Height             | 15.0 cm |
| Package 2 Width              | 5.0 cm  |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                              |          |
|------------------------------|----------|
| Package 2 Length             | 17.0 cm  |
| Package 2 Weight             | 88.0 g   |
| Unit Type Of Package 3       | S02      |
| Number Of Units In Package 3 | 800      |
| Package 3 Height             | 15.0 cm  |
| Package 3 Width              | 30.0 cm  |
| Package 3 Length             | 40.0 cm  |
| Package 3 Weight             | 7.352 kg |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

✓ Halogen Free Plastic Parts Product

## Certifications & Standards

|                       |   |
|-----------------------|---|
| Reach Regulation      | <a href="#">REACH Declaration</a>   |
| Eu Rohs Directive     | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a>           |
| China Rohs Regulation | <a href="#">China RoHS declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Circularity Profile   | No need of specific recycling operations  |