

Product data sheet

Specifications



Plug-in bridge, Linergy TR, 2 points,
for 4mm² terminal blocks, 2 way,
red, set of 10

NSYTRAL42

Main

Range	Linergy
Product Name	Linergy TR
Product Or Component Type	Plug-in bridge
Device Short Name	TRA
Accessory / Separate Part Category	Connection accessory
Product Compatibility	TRV screw terminal terminal block TRP push-in terminal block TRR spring terminal terminal block TRH IDC terminal block
Number Of Ways	2 ways

Complementary

Cable Cross Section	4 mm ²
Number Of Connections	4 3 2
Number Of Measurement Input	3 2 6 1 4
Quantity Per Set	Set of 10
Net Weight	2 g
Colour	Red

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.300 cm
Package 1 Width	1.200 cm
Package 1 Length	2.400 cm
Package 1 Weight	1.900 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	50
Package 2 Height	5.000 cm
Package 2 Width	15.000 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Length	17.000 cm
Package 2 Weight	97.000 g
Unit Type Of Package 3	S01
Number Of Units In Package 3	2000
Package 3 Height	15.000 cm
Package 3 Width	15.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	4.078 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

✓ Halogen Free Plastic Parts Product

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Circularity Profile	No need of specific recycling operations