

Product data sheet

Specifications



Switching jumper, Linergy TR, 4 points, for NSYTRV62TTD terminal, pluggable, orange, set of 10

NSYTRASJ4

Main

Range	Linergy
Product Name	Linergy TR
Product Or Component Type	Switching jumper
Device Short Name	TRA
Accessory / Separate Part Category	Measurement accessory
Product Compatibility	TRV screw terminal - passthrough terminal block, length = 100.8 mm TRV screw terminal - blade disconnect terminal block, length = 100.8 mm

Complementary

Cable Cross Section	6 mm ²
Number Of Connections	2
Number Of Measurement Input	6
Quantity Per Set	Set of 10
Net Weight	23.3 g
Colour	Orange

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.54 cm
Package 1 Width	2.54 cm
Package 1 Length	4.572 cm
Package 1 Weight	18.144 g
Unit Type Of Package 2	BAG
Number Of Units In Package 2	10
Package 2 Height	5 cm
Package 2 Width	15 cm
Package 2 Length	17 cm
Package 2 Weight	242 g

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Circularity Profile	No need of specific recycling operations