

Product data sheet

Specifications



Floor-Standing Server Rack 42U W800D1000 Fixed 19" Perf. Door R9011

NSYVDS42U810N

Main

| | |
|-----------------------------|---|
| Range | Actassi |
| Product name | Actassi VDS |
| Product or component type | 19" enclosure |
| Device application | Server |
| Applications | To mount 19" equipment To protect network connectivity equipment To mount server components |
| Enclosure type | Server cabinet |
| Support equipment | 4 x 19" uprights recessed of 120 mm from the front (pitch 25 mm) |
| Front face | Microperforated door |
| Door type | Front microperforated door - with 2 points locking system (key: 333) - reversible opening at 180 ° Rear microperforated door - with 2 points locking system (key: 333) - reversible opening at 180 ° |
| Accessibility for operation | Side Rear Top Front |
| Removable parts | Front door removable toolless Bottom blanking plate Rear door removable toolless Top blanking plate equipped with brush gasket Side panels |
| Colour | Door: black (RAL 9011) Panels: black (RAL 9011) Top and bottom: black (RAL 9011) Structure: black (RAL 9011) |

Complementary

| | |
|--------------------|--|
| Device composition | 2 x panels side 1 x assembled structure CBLX torx 1 x roof with removable blanking plate top 4 x levelling feets 4 x 19" uprights 1 x microperforated door (airflow 80%) front 1 x microperforated door (airflow 80%) rear |
| Load rating | 750 kg static |
| Back face | Microperforated door |
| Side face | Panel |
| Number of cut-out | 1 cut-outbottom 1 cut-outtop side panel 1 cut-outtop - split in 3 parts |
| Installation mode | Floor-standing |

| | |
|----------------------------|---|
| Material | Sheet steel: structure Sheet steel: door Sekurit glass: door Galvanized steel: upright Sheet steel: panel |
| Surface finish | Epoxy-polyester powder |
| Width | 800 mm |
| Height | 2000 mm |
| Depth | 1000 mm |
| Net weight | 129 kg |
| Number of rack unit | 42U |
| Targeted region | Europe |

Environment

| | |
|--------------------------------|------------------------------|
| IK degree of protection | IK08 conforming to IEC 62262 |
| IP degree of protection | IP20 conforming to IEC 60529 |
| Standards | IEC 60297-3-100 EIA-310D |

Packing Units

| | |
|-------------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Weight | 127.5 kg |
| Package 1 Height | 80 cm |
| Package 1 width | 100 cm |
| Package 1 Length | 200 cm |

Offer Sustainability

| | |
|-----------------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty | 18 months |
|-----------------|-----------|