

Product data sheet

Specifications



Data socket, New Unica, mechanism with fixing frame, RJ45, STP, straight, click, shuttered, aluminium

NU541730F

⚠ Discontinued

⚠ Discontinued on: Jun 30, 2023

Main

Range	New Unica
Product Or Component Type	Data socket
Device Application	Communication
Device Presentation	Mechanism with fixing frame
Colour Tint	Aluminium
Data Socket Type	RJ45 8 contact(s) Cat.6 < 250 MHz
Provided Equipment	Label holder Protective flap Fixing frame
Condition Of Use	Indoor

Complementary

Communication Network Type	1000BASE-TX
Communication Port Protocol	ATM 1200 Mbps
Number Of Modules	2 modules
Socket Number	1
Type Of Footprint	Infraplus
Connector Type	S-One
Cable Shielding Type	STP
Organization Of Wire	Shielded twisted pair
Connections - Terminals	Click
Device Mounting	Flush
Fixing Mode	Screws
Installation Direction	Straight
Material	Zamak: fixing frame Thermoplastic ABS-UV stabilised: central plate
Depth	40.5 mm
Width	74.5 mm
Height	74.5 mm
Embedding Depth	31.5 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Resistance To Chemical Agents	Resistant to alcohol (70 %)
	Resistant to alcohol (96 %)
	Resistant to A-Lactic Acid
	Resistant to diluted quaternary ammonium
	Resistant to diluted bleach
	Resistant to diluted ammonia
	Resistant to soapy water
	Resistant to crystal cleaner
	Resistant to hydrogen peroxide 10 volumes
	Resistant to hexane

Environment

Ip Degree Of Protection	IP20
Ik Degree Of Protection	IK01
Ambient Air Temperature For Operation	-25...55 °C
Ambient Air Temperature For Storage	-25...55 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.45 cm
Package 1 Width	7.45 cm
Package 1 Length	4.05 cm
Package 1 Weight	0.001 g