


Product data sheet

Specifications



Dardo Plus - control unit - rechargeable internal battery

OVA34210E

 **Discontinued on:** Dec 21, 2021

 **Discontinued**

Main

Product Or Component Type	Control unit
Function	Addressable
Supply	Rechargeable internal battery
Language	Norwegian Italian German Lituanien English Swedish Danish Finnish

Complementary

[Ue] Rated Operational Voltage	220 V 50 Hz
Power Consumption In Va	2 VA
Rated Voltage	6 V 0.8 Ah Ni-Cd (Nickel-Cadmium) battery
Autonomy	0.5...1 h depending on the number of lights connected
Charging Time	24 s
Output Type	Line 1 <1000 m
Operating Distance	2 200 m with 1 mm² 100 2 400 m with 1.5 mm² 100 2 600 m with 2.5 mm² 100

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	25.5 cm
Package 1 Width	11.8 cm
Package 1 Length	37 cm
Package 1 Weight	910 g

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Under investigation
