

Product data sheet

Specifications



Exiway One - emergency light block - addressable - maintained - 3 h - 220 lm

OVA34327

 **Discontinued on:** Feb 22, 2021

 **Discontinued**

Main

Range	Exiway
Product Name	Exiway One
Product Or Component Type	Emergency luminaire
Device Application	Lighting
Function	Addressable
Operational Mode	Maintained
Number Of Batteries	1 x 6 V 4 Ah Ni-Cd (Nickel-Cadmium)
Light Source	Fluorescent tube 2G11 24 W
Light Source Colour	White
Cover Type	Transparent
Wiring Device Additional Information	Can be inhibited with rest mode via Dardo Plus control unit

Complementary

Range Compatibility	Dardo Plus control unit
[Ue] Rated Operational Voltage	220...230 V AC/DC 50 Hz
Power Consumption In Va	27.9 VA
Power Consumption In W	13.8 W
Current Consumption	27 mA
Electrical Insulation Class	Class II
Autonomy	3 h
Charging Time	24 h
Type Of Glass	Fresnel glass
Device Mounting	Surface ceiling Hanging ceiling Flush false ceiling Flush wall Surface wall Electrified track
Material	Housing: plastic Cover: plastic
Height	160 mm
Depth	68 mm
Width	375 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Ip Degree Of Protection	IP65
Ik Degree Of Protection	IK07
Fire Resistance	850 °C
Product Certifications	IMQ
Ambient Air Temperature For Operation	0...40 °C
Standards	EN/IEC 60598-2-22 IEC 60695-2-10

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	1.77 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency

Well-being performance

✓ Toxic Heavy Metal Free	
✓ Mercury Free	
✓ Rohs Exemption Information	Yes
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile