


# Product data sheet

Specifications



## Luxa - emergency light block - standard - non-maintained - 3 h - 115 lm

OVA37198E

 **Discontinued on:** Dec 31, 2015

 **Discontinued**

### Main

Range Of Product	Luxa
Product Or Component Type	Emergency light fitting
Function	Standard
Supply	Non-maintained
Light Source	Fluorescent tube 2G7 11 W
Number Of Batteries	1 x 6 V 2.2 Ah Ni-Cd (Nickel-Cadmium)
Wiring Device Additional Information	Personalized with coloured frames Can be inhibited with rest mode via Teleur range of remote controls Adaptable exit sign

### Complementary

[Ue] Rated Operational Voltage	230 V 50 Hz
Power Consumption In Va	5 VA
Electrical Insulation Class	Class II
Autonomy	3 h
Charging Time	24 h
Luminous Flux	Emergency condition: 115 lm
Device Mounting	Surface ceiling Electrified track Flush false ceiling Flush wall Hanging ceiling Surface wall
Height	125 mm
Width	288 mm
Depth	58 mm
Net Weight	1.07 kg
Market Segment	Small commercial

### Environment

Ip Degree Of Protection	IP65
Ik Degree Of Protection	IK08
Ambient Air Temperature For Operation	0...40 °C
Fire Resistance	850 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	EN 60695-2-10 IEC 50-11 EN 60598-2-22 IEC 695-2-1
-----------	--

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.8 cm
Package 1 Width	13.2 cm
Package 1 Length	33 cm
Package 1 Weight	0.95 kg

## Contractual warranty

Warranty	18 months
----------	-----------