

Product data sheet

Specifications



Lys - emergency exit sign - self-diagnosis - maintained - 3 h

OVA38082

⚠ Discontinued on: Apr 19, 2021

⚠ Discontinued

Main

Range	Exiway
Product Name	Lys
Product Or Component Type	Emergency exit sign
Device Application	Signalling
Function	Self-test
Supply	Maintained depending on wiring Non-maintained depending on wiring
Colour	White
Light Source Colour	White
Cover Type	Transparent

Complementary

Range Compatibility	TBS remote control
[Ue] Rated Operational Voltage	200...230 V AC/DC
Power Consumption In Va	4.5 VA
Current Consumption	19 mA
Electrical Insulation Class	Class I
Battery Capacity	1.5 Ah at 4.8 V, Ni-Cd (Nickel-Cadmium)
Autonomy	3 h
Charging Time	24 h
Bulb Type	LED
Luminous Flux	Maintained mode: 35 lm Emergency condition: 35 lm
Visibility Distance	25 m
Indicator Type	Indicator two sides
Material	Plastic: cover Steel: housing
Device Mounting	Flag wall Flush
Height	245 mm
Width	360 mm
Depth	55 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Net Weight	1.8 kg
------------	--------

Environment

Ip Degree Of Protection	IP42
Ik Degree Of Protection	IK07
Ambient Air Temperature For Operation	0...40 °C
Fire Resistance	850 °C
Standards	EN 60598-2-22 EN 1838 IEC 50-11 IEC 695-2-1

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.7 cm
Package 1 Width	5.9 cm
Package 1 Length	37.5 cm
Package 1 Weight	1.87 kg

Contractual warranty

Warranty	18 months
----------	-----------