

Product data sheet

Specifications



Emergency Lighting, Exiway, Easysign, Standard, IP40, 24 m, LED, SA-SE, 3 h, White

OVA38251

Main

Range	Exiway
Product name	Exiway Easysign
Product or component type	Emergency exit sign
Device application	Lighting
Function	Standard
Supply	Maintained Non-maintained
Number of batteries	1 LiFePO4
Colour	White (RAL 9010)
Light source	1 x LED
Visibility distance	24 m

Complementary

[Ue] rated operational voltage	230 V AC 50/60 Hz
Electrical insulation class	Class II
LED lifespan	100000 h
Autonomy	3 h
Local signalling	Indicator light
Device mounting	Recessed ceiling
Material	Plastic self-extinguishing
Height	170 mm
Depth	31 mm
Width	260 mm

Environment

IP degree of protection	IP40
IK degree of protection	IK04
Ambient air temperature for operation	0...40 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	657.0 g
Package 1 Height	3.1 cm
Package 1 width	17 cm
Package 1 Length	26 cm
Unit Type of Package 2	P12
Number of Units in Package 2	32
Package 2 Weight	38.888 kg
Package 2 Height	50 cm
Package 2 width	80 cm
Package 2 Length	120 cm
Unit Type of Package 3	S03
Number of Units in Package 3	4
Package 3 Weight	3.361 kg
Package 3 Height	30 cm
Package 3 width	30 cm
Package 3 Length	40 cm

Offer Sustainability

EU RoHS Directive	Under investigation
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins