

# Product data sheet

Specifications



## Exiway Easyled - emergency light luminaire - std - non-maintained - 1 h - 70 lm

OVA38351

### Main

Range	Exiway
Aesthetic name	Exiway Easyled
Product or component type	Emergency light fitting
Device application	Lighting
Function	Standard
Supply	Non-maintained
Number of batteries	1 x 3.6 V 0.8 Ah Ni-Cd (Nickel-Cadmium)
Colour	White
Light source	LED integral LED 2 x 0.5 W
Light source colour	White
Cover type	Transparent
Wiring device additional information	Can be inhibited with rest mode via Teleur range of remote controls

### Complementary

[Ue] rated operational voltage	220...230 V AC 50/60 Hz
Power consumption in VA	2.4 VA
Power consumption in W	1.6 W
Current consumption	10 mA
Electrical insulation class	Class II
Autonomy	1 h
Charging time	12 h
Luminous flux	Emergency condition: 70 lm
Type of glass	Serigraphed transparent glass
Material	Plastic: housing Plastic: cover
Device mounting	Flush wall Surface wall Surface ceiling Flush false ceiling
Height	37 mm
Width	292.5 mm

Depth	116.5 mm
Net weight	0.47 kg

## Environment

IP degree of protection	IP42
IK degree of protection	IK07
Ambient air temperature for operation	5...30 °C
Fire resistance	850 °C
Product certifications	AENOR ENEC
Standards	EN/IEC 60598-2-22 IEC 60695-2-10

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	525.0 g
Package 1 Height	4.5 cm
Package 1 width	12.5 cm
Package 1 Length	30 cm
Unit Type of Package 2	S03
Number of Units in Package 2	12
Package 2 Weight	6.703 kg
Package 2 Height	30 cm
Package 2 width	30 cm
Package 2 Length	40 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>

## Contractual warranty

Warranty	18 months
----------	-----------