



Main

Range	Exiway
Product name	Exiway Easyled
Product or component type	Emergency light fitting
Function	Self-test
Supply	Maintained
Number of batteries	1 x 3.6 V 1.6 Ah Ni-Cd (Nickel-Cadmium)
Light source	Integral LED 4 x 0.5 W
Wiring device additional information	Can be inhibited with rest mode via Teleur range of remote controls

Complementary

[Ue] rated operational voltage	230 V AC 50/60 Hz
Power consumption in VA	4 VA
Electrical insulation class	Class II
Autonomy	1 h
Charging time	12 h
Type of glass	Serigraphed transparent glass
Device mounting	Surface ceiling Flush false ceiling Flush wall Surface wall
Height	292 mm
Depth	37 mm
Width	116 mm
Product weight	0.53 kg

Environment

IP degree of protection	IP65
IK degree of protection	IK07
Fire resistance	850 °C
Product certifications	ENEC
Ambient air temperature for operation	0...40 °C

Standards	EN/IEC 60598-2-22 EMC directive EN 60598-1 EN 62471
-----------	--

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	535 g
Package 1 Height	3.8 cm
Package 1 width	11.7 cm
Package 1 Length	29.3 cm

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information