

# Product data sheet

Specifications



## Exiway Class- emergency light block - self-diagnosis - maintained - 2 h - 260 lm

OVA38569

⚠ Discontinued on: Feb 22, 2021

⚠ Discontinued

### Main

Range	Exiway
Product Name	Exiway Class
Product Or Component Type	Emergency luminaire
Device Application	Lighting
Function	Self-test
Operational Mode	Maintained
Number Of Batteries	1 x 6 V 2.5 Ah Ni-Cd (Nickel-Cadmium)
Light Source	LED 11 W
Light Source Colour	White
Wiring Device Additional Information	Can be inhibited with rest mode via Teleur range of remote controls

### Complementary

Range Compatibility	TBS remote control
[Ue] Rated Operational Voltage	220...230 V AC/DC 50 Hz
Power Consumption In Va	5.6 VA non-maintained 14 VA maintained
Power Consumption In W	1.5 W non-maintained 6.7 W maintained
Current Consumption	24 mA
Electrical Insulation Class	Class II
Autonomy	2 h
Charging Time	12 h
Type Of Glass	Mineral glass
Device Mounting	Flush wall Surface wall
Material	Housing: plastic Cover: glass
Height	223 mm
Depth	51 mm
Width	303 mm
Net Weight	1.69 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

Ip Degree Of Protection	IP42
Ik Degree Of Protection	IK07
Fire Resistance	850 °C
Product Certifications	IMQ CE
Ambient Air Temperature For Operation	0...40 °C
Standards	EN/IEC 60598-2-22 IEC 60695-2-10 EN/IEC 62471

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7 cm
Package 1 Width	24.4 cm
Package 1 Length	33 cm
Package 1 Weight	2.44 kg

## Contractual warranty

Warranty	18 months
----------	-----------