

Product data sheet

Specifications



Exiway Class- emergency light block- self-diagnosis- non-maintained- 2 h- 350 lm

OVA38570

⚠ Discontinued on: Feb 22, 2021

⚠ Discontinued

Main

Range	Exiway
Product Name	Exiway Class
Product Or Component Type	Emergency luminaire
Device Application	Lighting
Function	Self-test
Operational Mode	Non-maintained
Number Of Batteries	1 x 4.8 V 4 Ah Ni-Cd (Nickel-Cadmium)
Light Source	LED 24 W
Light Source Colour	White
Wiring Device Additional Information	Can be inhibited with rest mode via Teleur range of remote controls

Complementary

Range Compatibility	TBS remote control
[Ue] Rated Operational Voltage	220...230 V AC/DC 50 Hz
Power Consumption In Va	5.6 VA
Power Consumption In W	1.3 W
Current Consumption	24 mA
Electrical Insulation Class	Class II
Autonomy	2 h
Charging Time	12 h
Type Of Glass	Mineral glass
Device Mounting	Flush wall Surface wall
Material	Housing: plastic Cover: glass
Height	223 mm
Depth	51 mm
Width	303 mm
Net Weight	1.79 kg

Environment

Ip Degree Of Protection	IP42
Ik Degree Of Protection	IK07
Fire Resistance	850 °C
Product Certifications	IMQ CE
Ambient Air Temperature For Operation	0...40 °C
Standards	EN/IEC 60598-2-22 IEC 60695-2-10 EN/IEC 62471

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.6 cm
Package 1 Width	25 cm
Package 1 Length	33.8 cm
Package 1 Weight	2.167 kg

Contractual warranty

Warranty	18 months
-----------------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency

Well-being performance

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Eu Rohs Directive Compliant
[EU RoHS Declaration](#)

China Rohs Regulation [China RoHS declaration](#)
Pro-active China RoHS declaration (out of China RoHS legal scope)

Environmental Disclosure [Product Environmental Profile](#)
