

Product data sheet

Specifications



Exiway One - emergency light block - self-diagnosis - maintained - 1 h - 380 lm

OVA38781

 **Discontinued on:** Feb 22, 2021

 **Discontinued**

Main

Range	Exiway
Product Name	Exiway One
Product Or Component Type	Emergency luminaire
Function	Self-test
Operational Mode	Maintained
Number Of Batteries	1 x 4.8 V 4 Ah Ni-Cd (Nickel-Cadmium)
Light Source	Fluorescent tube G5 8 W
Wiring Device Additional Information	Can be inhibited with rest mode via Teleur range of remote controls

Complementary

Range Compatibility	TBS remote control
[Ue] Rated Operational Voltage	230 V 50 Hz
Power Consumption In Va	24.2 VA
Power Consumption In W	10.3 W
Electrical Insulation Class	Class II
Autonomy	1 h
Charging Time	12 h
Type Of Glass	Fresnel glass
Device Mounting	Surface ceiling Hanging ceiling Flush false ceiling Flush wall Surface wall Electrified track
Height	160 mm
Depth	68 mm
Width	375 mm

Environment

Ip Degree Of Protection	IP65
Ik Degree Of Protection	IK07
Fire Resistance	850 °C
Product Certifications	ENEC

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Operation	0...40 °C
Standards	EN/IEC 60598-2-22 IEC 60695-2-10

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency

Well-being performance

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Eu Rohs Directive [Compliant](#)
[EU RoHS Declaration](#)

China Rohs Regulation [China RoHS declaration](#)
Pro-active China RoHS declaration (out of China RoHS legal scope)

Environmental Disclosure [Product Environmental Profile](#)