

Product data sheet

Specifications



Toplux - portable emergency lamp - 490 lm - 4 h

OVA41319E

Main

Range Of Product	Toplux
Product Or Component Type	Portable emergency lamp
Device Application	Lighting
Colour	Green
Wiring Device Additional Information	Colour filters included Long distance light beam with range of 200 m

Complementary

[Ue] Rated Operational Voltage	230 V 50 Hz
Power Consumption In Va	10 VA
Device Composition	Charging unit
Battery Capacity	7 Ah at 6 V, Ni-Cd (Nickel-Cadmium)
Charging Time	24 h
Bulb Type	Halogen 10 W main lamp Incandescent 1.5 W auxiliary lamp
Autonomy	24 h auxiliary lamp 4 h main lamp
Luminous Flux	490 lm 2 m main lamp 5 lm 1 m auxiliary lamp
Operating Mode Options	Main lamp: blinking Auxiliary lamp: blinking
Enclosure Material	Plastic
Electrical Insulation Class	Class II
Length	262 mm
Height	165 mm
Width	120 mm
Net Weight	2.4 kg

Environment

Ip Degree Of Protection	IP55
Ambient Air Temperature For Operation	-10...40 °C
Standards	IEC 2.2

Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.6 cm
Package 1 Width	17.0 cm
Package 1 Length	23.5 cm
Package 1 Weight	2.681 kg
Unit Type Of Package 2	S03
Number Of Units In Package 2	4
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	11.255 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information