

Product data sheet

Specifications

KIT EVERLUX J65E - conversion kit

OVA43010



⚠ Discontinued on: Feb 22, 2021

⚠ Discontinued

Main

Range	Evx
Aesthetic Name	Evx Ferro
Product Or Component Type	Conversion kit
Function	Standard

Complementary

[Ue] Rated Operational Voltage	230 V 50 Hz
Rated Power In Va	5 VA
Battery Capacity	4 Ah 6 V Ni-Cd (Nickel-Cadmium)
Charging Time	1 h 2.1 h 2.45 s
Emergency Luminous Flux	100 % of nominal flux during 2 h 10 10 W G3 100 % of nominal flux during 1 h 20 W G3 10 % of nominal flux during 2 h 45 20 W G3 10 % of nominal flux during 1 h 50 W GY6.35
Bulb Type	Halogen lamp
Electrical Insulation Class	Class II
Connections - Terminals	Screw terminal
Height	Battery: 33 mm Circuit: 32 mm
Width	Battery: 332 mm Circuit: 183 mm
Depth	Circuit: 40.5 mm Battery: 34 mm
Net Weight	0.75 kg 0.25 kg

Environment

Fire Resistance	750 °C
Standards	CEI 50-11 IEC 695-2-1

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	4 cm
Package 1 Width	8 cm
Package 1 Length	34.5 cm
Package 1 Weight	500 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency

Well-being performance

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Eu Rohs Directive [Compliant](#)
[EU RoHS Declaration](#)

China Rohs Regulation [China RoHS declaration](#)
Pro-active China RoHS declaration (out of China RoHS legal scope)

Environmental Disclosure [Product Environmental Profile](#)