

Product data sheet

Specifications



Evx Ferro - con kit - self-test - up to 58W 3h

OVA43076

 **Discontinued on:** Apr 19, 2021

 **Discontinued**

Main

Range	Evx
Aesthetic Name	Evx Ferro
Product Or Component Type	Conversion kit
Device Application	Lighting
Function	Self-test
Wiring Device Additional Information	Can be inhibited with rest mode via remote control

Complementary

[Ue] Rated Operational Voltage	230 V 50 Hz
Rated Power In Va	8 VA
Battery Capacity	4 Ah 7 V Ni-Cd (Nickel-Cadmium) in line
Charging Time	24 h
Emergency Luminous Flux	14 % of nominal flux during 3 h 36 W T8
Bulb Type	Indicator LED
Ballast Type	Electromagnetic ballast
Electrical Insulation Class	Class II
Connections - Terminals	Screw terminals
Device Connection	Connection to remote switch
Height	Battery: 34 mm Circuit: 32 mm
Width	Battery: 197 mm Circuit: 485 mm
Depth	Battery: 39 mm Circuit: 40 mm
Net Weight	1.3 kg

Environment

Fire Resistance	750 °C
Standards	EN 61347-2-7 EN 60695-2-1

Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
Package 1 Height	55 cm
Package 1 Width	9 cm
Package 1 Length	4.5 cm
Package 1 Weight	1.3 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency

Well-being performance

✓ Toxic Heavy Metal Free	
✓ Mercury Free	
✓ Rohs Exemption Information	Yes
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile