

Product data sheet

Specifications



Emergency luminaire, Exiway Smartled, 230V, 350lm, IP65, white

OVA48700

Main

Range	Exiway
Product Name	Exiway Smartled
Product Or Component Type	Emergency luminaire
Device Application	Anti-panic lighting
Function	Centralized
Operational Mode	Non-maintained
Light Source	9 x LED 0.5 W
Visibility Distance	24 m

Complementary

[Ue] Rated Operational Voltage	230 V AC 50/60 Hz 216 V DC
Power Consumption In Va	9.4 VA
Power Consumption In W	4.6 W
Electrical Insulation Class	Class II
Led Lifespan	100000 h
Test Function	Automatic periodical functional & duration test
Luminous Flux	Emergency condition: 350 lm
Device Mounting	Surface ceiling Flush false ceiling Flush wall Surface wall
Material	Housing: polycarbonate self-extinguishing Cover: plastic
Height	127 mm
Depth	45.5 mm
Width	300 mm
Net Weight	0.59 kg

Environment

Ip Degree Of Protection	IP65
Ik Degree Of Protection	IK07
Fire Resistance	850 °C
Product Certifications	ENEC

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Operation	0...40 °C
Standards	EN 60598-2-22: II EN 62471 EN 60598-1

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.7 cm
Package 1 Width	4.5 cm
Package 1 Length	30.0 cm
Package 1 Weight	615.0 g

Contractual warranty

Warranty	18 Months
----------	-----------

Sustainability




Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration	
Eu Rohs Directive	Compliant	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)	