

Product data sheet

Specifications



battery - 4.8 V - 1.5 Ah - Ni-Cd

OVA51015E

⚠ Discontinued on: Dec 21, 2021

⚠ Discontinued

Main

Range	Exiway
Product Or Component Type	Battery
Device Application	Lighting
Number Of Cells	4
Body Type	Sealed

Complementary

Range Compatibility	Exiway Quick Signal emergency exit sign Exiway Click Signal emergency exit sign
Product Compatibility	Quick signal 3 h
Battery Capacity	1.5 Ah at 4.8 V, Ni-Cd (Nickel-Cadmium)
Battery Size	KRMT 23/43
Diameter	23 mm
Length	86 mm
Height	45 mm
Width	23 mm
Net Weight	0.2 kg

Environment

Ambient Air Temperature For Operation	-10...50 °C
---------------------------------------	-------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11 cm
Package 1 Width	5 cm
Package 1 Length	9 cm
Package 1 Weight	200 g

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency

Eu Rohs Directive

Not applicable, out of EU RoHS legal scope

Environmental Disclosure

[Product Environmental Profile](#)