

Product data sheet

Specifications



3-Pole Circuit Breaker, 125A, T3 Type for Symmetra PX250/500kW

PD3P125AT3B

Overview

Lead TimeSpecial Order - Call for Quoted Lead Times

Main

Main Input Voltage	480 V 3 phases 400 V 3 phases
Main Output Voltage	480 V 3 phases 400 V 3 phases
Output Connector Type	Hard wire 3-wire (3P) 1
Provided Equipment	Installation guide

Physical

Height	43.2 cm
Width	55.9 cm
Depth	54.6 cm
Net Weight	2.77 kg
Mounting Location	Front
Mounting Preference	No preference
Mounting Mode	Not rack-mountable

Input

Max Line Current	125 A
Network Frequency	50 Hz 60 Hz

Output

Max Current Draw	125 A
------------------	-------

Conformance

Product Certifications	CE UL listed
------------------------	-----------------

Environmental

Ambient Air Temperature For Operation	0...40 °C
Ambient Air Temperature For Storage	-15...40 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	43.2 cm
Package 1 Width	54.6 cm
Package 1 Length	55.9 cm
Package 1 Weight	3.7 kg

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Under investigation
