

# Product data sheet

Specifications



## 3-Pole Circuit Breaker, 200A, T3 Type for Symmetra PX250/500kW

PD3P200AT3B

### Overview

Lead Time	Special Order - Call for Quoted Lead Times
-----------	--

### Main

Main Input Voltage	480 V 3 phases 400 V 3 phases
Main Output Voltage	480 V 3 phases 400 V 3 phases
Output Connector Type	Hard wire 3-wire (3P) 1
Provided Equipment	Installation guide

### Physical

Height	43.2 cm
Width	55.9 cm
Depth	54.6 cm
Net Weight	2.82 kg
Mounting Location	Front
Mounting Preference	No preference
Mounting Mode	Not rack-mountable

### Input

Max Line Current	200 A
Network Frequency	50 Hz 60 Hz

### Output

Max Current Draw	200 A
------------------	-------

### Conformance

Product Certifications	CE UL listed
------------------------	-----------------

### Environmental

Ambient Air Temperature For Operation	0...40 °C
Ambient Air Temperature For Storage	-15...40 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	43.2 cm
Package 1 Width	54.6 cm
Package 1 Length	55.9 cm
Package 1 Weight	3.7 kg

## Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------

# Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Under investigation