

Product data sheet

Specifications



APC Home Office SurgeArrest 8 Outlets, 120V White

PH8W

⚠ To be discontinued on: Apr 30, 2024

⚠ To be discontinued

Overview

Lead Time Usually in Stock

Main

Main Input Voltage	120 V
Input Connection Type	NEMA 5-15P
Cable Length	1.83 m
Number Of Cables	1
Provided Equipment	User manual

Physical

Colour	White
Height	3 cm
Width	7.7 cm
Depth	24.7 cm
Net Weight	0.6 kg
Mounting Preference	No preference
Mounting Mode	Not rack-mountable

Input

Maximum Line Current	15 A
Network Frequency	50/60 Hz
Maximum Input Current	15 A
Switching Current Capacity	15 A

Output

Number Of Power Socket Outlets	8
Outlet Standard	NEMA 5-15R

Conformance

Product Certifications	MET Canada MET USA
------------------------	-----------------------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	UL 1363
	UL 1449
Equipment Protection Policy	Lifetime : \$150000

Environmental

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 % non-condensing
Operating Altitude	0...10000 ft
Ambient Air Temperature For Storage	-15...45 °C
Storage Relative Humidity	0...95 % non-condensing
Storage Altitude	0.00...15240.00 m

Surge Protection and Filtering

Response Time	1 ns common mode
Common Mode Rejection	40 dB
Peak Current	56 kAcommon mode 28 kAnormal mode
Surge Energy Rate	2160 J

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.8 cm
Package 1 Width	28.5 cm
Package 1 Length	14.5 cm
Package 1 Weight	0.7 kg
Scc14	10731304336164

Contractual warranty

Warranty	Limited Lifetime
----------	------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant with Exemptions

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)