

Product data sheet

Specifications



Unika interlocked socket - 63 A - 3P + N + E - 100...130 V AC - IP65 - wall

PKB63R515

⚠ Discontinued on: Jun 30, 2022

⚠ Discontinued

Main

Range	PratiKa
Product Or Component Type	Interlocked socket
Device Short Name	Unika socket
Plug, Socket Category	Low voltage
Poles Description	3P + N + E
Network Type	AC
Outlet Standard	Industrial

Complementary

Mounting Mode	Wall-mounted
[In] Rated Current	63 A
[Ue] Rated Operational Voltage	100...130 V
Network Frequency	50/60 Hz
Ground Lug Clockwise Position	4 h
Protection Type	Fuse
Fuse Type	Cylindrical
Fuse Size	10.3 x 38 mm
Plug, Socket Material	Housing: self-extinguishing polymer
Contacts Material	Pins: stainless steel Screws: stainless steel
Connections - Terminals	Captive screws
Maximum Cable Cross Section	35 mm²
Maximum Cable Outer Diameter	25 mm
Cable Entry	Cable gland
Thread Type	Pg 21
Net Weight	3 kg
Base Dimension	140 x 430 mm
Height	430 mm
Width	140 mm
Depth	190 mm
Colour	Grey (RAL 7035)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Voltage Colour	Yellow
----------------	--------

Environment

Standards	IEC 60309-1 IEC 60309-2
Ip Degree Of Protection	IP65 conforming to IEC 60529
Ik Degree Of Protection	IK09 conforming to EN 62262
Fire Resistance	750 °C conforming to IEC 60695-2-11
Relative Humidity	50 % at 40 °C 70 % at 30 °C 90 % at 20 °C
Ambient Air Temperature For Operation	35 °C (86400 s) -25...40 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	19.5 cm
Package 1 Width	14 cm
Package 1 Length	43 cm
Package 1 Weight	3.7 kg

Contractual warranty

Warranty	18 months
----------	-----------