

# Product data sheet

Specifications



## PratiKa wander plug - straight - 16 A - 3P + N + E - 100...130 V AC - IP67

PKE16M715

⚠ Discontinued on: Jun 30, 2022

⚠ Discontinued

### Main

Range	PratiKa
Product Or Component Type	Wander plug
Device Short Name	PratiKa plug
Plug, Socket Category	Low voltage
Poles Description	3P + N + E
Network Type	AC
Outlet Standard	Industrial

### Complementary

Plug, Socket, Control Station Shape	Straight
[In] Rated Current	16 A
[Ue] Rated Operational Voltage	100...130 V
Network Frequency	50/60 Hz
Ground Lug Clockwise Position	4 h
Plug, Socket Material	Housing: self-extinguishing engineering polymer
Contacts Material	Sleeves: brass
Connections - Terminals	Captive screws
Cable Cross Section	1...4 mm²
Cable Outer Diameter	8...15 mm
Cable Entry	Fair lead Cable gland
Thread Type	Pg 21
Net Weight	0.22 kg
Height	142 mm
Width	89 mm
Depth	89 mm
Colour	Grey (RAL 7035)
Voltage Colour	Yellow

### Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	IEC 60309-2 IEC 60309-1
Ip Degree Of Protection	IP67 conforming to IEC 60529
Ik Degree Of Protection	IK08 conforming to EN 62262
Fire Resistance	850 °C conforming to IEC 60695-2-11
Relative Humidity	50 % at 40 °C 70 % at 30 °C 90 % at 20 °C
Operating Altitude	2000 m
Ambient Air Temperature For Operation	35 °C ( 86400 s ) -25...40 °C

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	26.3 cm
Package 1 Width	27 cm
Package 1 Length	17 cm
Package 1 Weight	220 g

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance



Rohs Exemption Information

Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations