


# Product data sheet

Specifications



## PratiKa socket - screw - angled - 32A - 3P + E - 100...130 V AC - wall

PKF32W414

### Main

Range	PratiKa
Product Or Component Type	Socket
Device Short Name	PratiKa socket
Plug, Socket Category	Low voltage
Poles Description	3P + E
Network Type	AC
Outlet Standard	Industrial

### Complementary

Mounting Mode	Wall-mounted
Plug, Socket, Control Station Shape	Angled
[In] Rated Current	32 A
[Ue] Rated Operational Voltage	100...130 V
Network Frequency	50/60 Hz
Ground Lug Clockwise Position	4 h
Plug, Socket Material	Housing: self-extinguishing engineering polymer
Contacts Material	Sleeves: brass
Connections - Terminals	Captive screws
Cable Cross Section	2.5...10 mm²
Cable Outer Diameter	21 mm
Thread Type	M25
Net Weight	0.3 kg
Height	160 mm
Width	90 mm
Depth	119 mm
Colour	Grey (RAL 7035)
Voltage Colour	Yellow

### Environment

Standards	IEC 60309-1 IEC 60309-2
Ip Degree Of Protection	IP44 conforming to IEC 60529

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

<b>Ik Degree Of Protection</b>	IK08 conforming to EN 62262
<b>Fire Resistance</b>	750 °C conforming to IEC 60695-2-1
<b>Relative Humidity</b>	50 % at 40 °C 70 % at 30 °C 90 % at 20 °C
<b>Ambient Air Temperature For Operation</b>	35 °C ( 86400 s ) -25...40 °C

## Packing Units

<b>Unit Type Of Package 1</b>	PCE
<b>Number Of Units In Package 1</b>	1
<b>Package 1 Height</b>	11.9 cm
<b>Package 1 Width</b>	9 cm
<b>Package 1 Length</b>	16 cm
<b>Package 1 Weight</b>	260 g
<b>Unit Type Of Package 2</b>	BB1
<b>Number Of Units In Package 2</b>	6
<b>Package 2 Height</b>	17 cm
<b>Package 2 Width</b>	27 cm
<b>Package 2 Length</b>	26.3 cm
<b>Package 2 Weight</b>	1.76 kg
<b>Unit Type Of Package 3</b>	S03
<b>Number Of Units In Package 3</b>	12
<b>Package 3 Height</b>	30 cm
<b>Package 3 Width</b>	30 cm
<b>Package 3 Length</b>	40 cm
<b>Package 3 Weight</b>	4.007 kg

## Contractual warranty

<b>Warranty</b>	18 months
-----------------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations