

Product data sheet

Specifications



APC Performance SurgeArrest 6 outlets 230V Germany

PM6-GR

⚠ To be discontinued on: Apr 30, 2024

⚠ To be discontinued

Overview

Lead Time Usually in Stock

Main

Main Input Voltage	230 V
Input Connection Type	Schuko CEE 7/7P
Cable Length	2.00 m
Number Of Cables	1
Provided Equipment	User manual

Physical

Colour	White
Height	6.17 cm
Width	27.15 cm
Depth	11.03 cm
Net Weight	0.69 kg
Mounting Preference	No preference
Mounting Mode	Rack-mounted

Input

Input Power	2300 W
Network Frequency	50 Hz
Maximum Input Current	10 A
Switching Current Capacity	10 A

Output

Number Of Power Socket Outlets	6
Outlet Standard	Schuko CEE 7

Conformance

Product Certifications	CE
Equipment Protection Policy	Lifetime : 50000 euros

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environmental

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 % non-condensing
Operating Altitude	0...50000 ft
Ambient Air Temperature For Storage	-15...45 °C
Storage Relative Humidity	0...95 %
Storage Altitude	0.00...15240.00 m

Surge Protection and Filtering

Response Time	1 ns common mode
Common Mode Rejection	40 dB
Peak Current	48 kAcommon mode
Surge Energy Rate	1836 J

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.5 cm
Package 1 Width	31 cm
Package 1 Length	16.5 cm
Package 1 Weight	0.83 kg
Scc14	10731304313714

Contractual warranty

Warranty	Limited Lifetime (European Union countries only)
----------	--------------------------------------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information