

Product data sheet

Specifications



Pragma transparent door - for enclosure - 1 x 24 modules

PRA15124

 **Discontinued on:** Oct 31, 2023

 **Discontinued**

Main

Range	Pragma
Product Or Component Type	Door
Accessory / Separate Part Category	Enclosure accessories
Market Segment	Small commercial Residential

Complementary

Enclosure Mounting	Flush Surface
Key Number	Number to be stated
Type Of Front Cover	Transparent
Door Opening Side	Right or left
Number Of Horizontal Rows	1
9 Mm Pitches	48
Number Of 18 Mm Modules Per Row	24
Total Number Of 18 Mm Modules	24
Installation Description	Surface mounting Flush mounting
Enclosure Material	Glass Metal
Width	550 mm
Height	300 mm
Depth	20 mm
Colour	Colourless

Environment

Fire Resistance	750 °C
Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK09
Ambient Air Temperature For Operation	-25...60 °C
Ambient Air Temperature For Storage	-25...60 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.000 cm
Package 1 Width	65.000 cm
Package 1 Length	39.000 cm
Package 1 Weight	3.700 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	43
Package 2 Height	120.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	171.100 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations