

# Product data sheet

Specifications



## Pragma flush enclosure - IP40 - 2 x 18 modules - transparent door

PRA24218

⚠ Discontinued on: Oct 31, 2023

⚠ Discontinued

### Main

Range	Pragma
Product Or Component Type	Enclosure
Enclosure Type	Distribution enclosure
Width	456 mm wall: 486 mm outside:
Height	480 mm wall: 510 mm outside:
Depth	86 mm wall: 43 mm outside:
Nb Of 18 Mm Modules Per Row	18
Nb Of Horizontal Rows	2
Electrical Insulation Class	Class II Double insulation
Provided Equipment	2 x terminal block 1 x identification label 1 x marking kit 1 x blanking plate strip
Type Of Door	Transparent

### Complementary

Enclosure Mounting	Flush
9 Mm Pitches	36
Total Number Of 18 Mm Modules	36
Power Dissipation In W	62 W
[In] Rated Current	90 A
Type Of Rail	DIN
Mounting Plate Description	Without mounting plate
Cable Entry	Removable plates Cable or tube Side pre-cutouts
Number Of Terminal Blocks	1 earth (Quick) with 24 outgoing 1 neutral (Quick) with 24 outgoing
Distribution Block Outgoers	3 x 25 mm² for earth 21 x 4 mm² for earth 3 x 25 mm² for neutral 21 x 4 mm² for neutral

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Enclosure Material	Back part: technoplastic Door: technoplastic Front face: technoplastic
Colour	Enclosure: white (RAL 9016) Front face: grey (RAL 7004) Door: colourless
Market Segment	Residential Small commercial
Embedding Depth	86 mm
Internal Depth	84 mm

## Environment

Fire Resistance	Back part: 650 °C Front face: 650 °C Door: 650 °C
Ip Degree Of Protection	IP30 without door IP40 with door
Ik Degree Of Protection	IK08 without door IK09 with door
Overvoltage Category	II
Ambient Air Temperature For Operation	-25...60 °C
Standards	IEC 60670-1 IEC 60670-24 IEC 61439-1 IEC 61439-3

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	17.500 cm
Package 1 Width	50.000 cm
Package 1 Length	52.000 cm
Package 1 Weight	5.637 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	8
Package 2 Height	90.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	57.096 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations