

# Product data sheet

Specifications



## Pragma flush enclosure - IP40 - 4 x 24 modules - transparent door

PRA26424

⚠ Discontinued on: Oct 31, 2023

⚠ Discontinued

### Main

Range	Pragma
Product Or Component Type	Enclosure
Enclosure Type	Distribution enclosure
Width	570 mm wall: 610 mm outside:
Height	780 mm wall: 810 mm outside:
Depth	95 mm wall: 55 mm outside:
Nb Of 18 Mm Modules Per Row	24
Nb Of Horizontal Rows	4
Electrical Insulation Class	Class II Double insulation
Provided Equipment	1 x identification label 1 x marking kit 1 x blanking plate strip
Type Of Door	Transparent

### Complementary

Enclosure Mounting	Flush
9 Mm Pitches	48
Total Number Of 18 Mm Modules	96
Power Dissipation In W	110 W
[In] Rated Current	160 A
Type Of Rail	Multifix
Mounting Plate Description	Without mounting plate
Cable Entry	Side pre-cutouts Removable plates Cable or tube
Enclosure Material	Back part: technoplastic Front face: technoplastic Back part: metal Front face: metal Door: glass Door: metal
Colour	Enclosure: white (RAL 9016) Front face: grey (RAL 7004) Door: colourless

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Targeted Country	Italy
Embedding Depth	95 mm
Internal Depth	93 mm

## Environment

Fire Resistance	Back part: 650 °C Front face: 650 °C Door: 650 °C
Ip Degree Of Protection	IP30 without door IP40 with door
Ik Degree Of Protection	IK08 without door IK09 with door
Overvoltage Category	II
Ambient Air Temperature For Operation	-25...60 °C
Standards	IEC 60670-1 IEC 60670-24 IEC 61439-1 IEC 61439-3

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	22.5 cm
Package 1 Width	65.0 cm
Package 1 Length	84.0 cm
Package 1 Weight	18.0 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	4
Package 2 Height	77.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	84.0 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations