

Product data sheet

Specifications



Decor - double 2-way - complete product - 10 A 250 V - ivory sahara

PRMS044022D

⚠ Discontinued on: Dec 30, 2019

⚠ End-of-service on: Jan 23, 2020

⚠ Discontinued

Main

Aesthetic Name	Decor
Product Or Component Type	Control switch
Device Presentation	Complete product
Type Of Packing	Flow-pack

Complementary

Switch Function	Double 2-way
Local Signalling	Without pilot light
[In] Rated Current	10 A
[Ue] Rated Operational Voltage	250 V AC
Material	ABS (acrylonitrile butadiene-styrene)
Number Of Modules	3
Embedding Depth	24.9 mm
Depth	33.9 mm
Length	123 mm
Height	9 mm
Width	85 mm
Connections - Terminals	Pillar terminals
Cable Cross Section	6 mm ²
Awg Gauge	AWG 8
Fixing Mode	Clip-in

Environment

Standards	ABNT NBR NM 60.669
-----------	--------------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	0.076 kg

Contractual warranty

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months