

Product data sheet

Specifications



Resi9 Retrofit kit from 2 to 3 Row

R9H13403R

⚠ Discontinued on: Sep 30, 2021

⚠ Discontinued

Main

Range	Resi9
Product Or Component Type	Retrofit
Accessory / Separate Part Category	Extension accessory
Nb Of 18 Mm Modules Per Row	13
Nb Of Horizontal Rows	3
Provided Equipment	1 x marking kit 1 x blanking plate
Range Compatibility	Resi9 enclosure Opale enclosure

Complementary

[In] Rated Current	90 A
Width	252 mm
Height	500 mm
Depth	108 mm
Colour	White (RAL 9003)

Environment

Ip Degree Of Protection	IP30 conforming to EN/IEC 60529
Ik Degree Of Protection	IK07 conforming to IEC 62262 IK07 conforming to EN 50102
Fire Resistance	750 °C conforming to EN/IEC 60695-2-11

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.5 cm
Package 1 Width	26 cm
Package 1 Length	52 cm
Package 1 Weight	1.56 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

China Rohs Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information