

Product data sheet

Specifications



APC Replacement Battery Cartridge #44 for EUROBAT with 2 Year Warranty

RBC44EB

Overview

| | |
|-----------|------------------|
| Lead Time | Usually in Stock |
|-----------|------------------|

Main

| | |
|---------------------------|--|
| Product Or Component Type | Replacement battery cartridge |
| Number Of Cables | 1 |
| Battery Type | Lead-acid battery |
| Provided Equipment | All required connectors Battery recycling guide Metallic battery tray or enclosure Reusable packaging Installation guide |

Batteries & Runtime

| | |
|--|---|
| Number Of Battery Free Slots | 0 |
| Number Of Battery Filled Slots | 0 |
| Device Mounting | Enclosed battery cartridge |
| Battery Voltage | 192 V |
| Additional Information | Each RBC44EB consists of 2 battery modules. |
| Number Of Battery Replacement Quantity | 1 |

Physical

| | |
|----------------|--------------------|
| Colour | Black |
| Height | 12.2 cm |
| Width | 19.7 cm |
| Depth | 59.7 cm |
| Net Weight | 34.56 kg |
| Mounting Mode | Not rack-mountable |
| Usb Compatible | No |

Environmental

| | |
|---------------------------------------|--------------|
| Ambient Air Temperature For Operation | 0...40 °C |
| Operating Altitude | 0...10000 ft |
| Relative Humidity | 0...95 % |
| Ambient Air Temperature For Storage | -15...45 °C |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|---------------------------|-------------------|
| Storage Altitude | 0.00...15240.00 m |
| Storage Relative Humidity | 0...95 % |

Packing Units

| | |
|------------------------------|----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 22.6 cm |
| Package 1 Width | 40.9 cm |
| Package 1 Length | 78.1 cm |
| Package 1 Weight | 37.28 kg |
| Unit Type Of Package 2 | PAM |
| Number Of Units In Package 2 | 12 |
| Package 2 Height | 91.2 cm |
| Package 2 Width | 100 cm |
| Package 2 Length | 120 cm |
| Package 2 Weight | 460 kg |

Contractual warranty

| | |
|----------|---------------------------|
| Warranty | 2 years repair or replace |
|----------|---------------------------|

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)




Take-back Transparency RoHS/REACH

Resource performance

 Take-Back Program Available

Well-being performance

 Rohs Exemption Information [Yes](#)

Certifications & Standards

| | |
|--------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End of Life Information |