

Product data sheet

Specifications



Cover frame, Odace Styl, 1 gang, white

S520722

Main

| | |
|---------------------------|-------------------|
| Range Of Product | Odace |
| Aesthetic Name | Odace Styl Pratic |
| Product Or Component Type | Cover frame |
| Number Of Gangs | 1 gang |
| Cover Type | Key holder |
| Type Of Frame | Single |
| Type Of Packing | Flow-pack |

Complementary

| | |
|-------------------------------|---|
| Device Mounting | Flush |
| Fixing Mode | Clip-in |
| Colour Tint | White (RAL 9003) |
| Surface Finish | Glossy |
| Material | Thermoplastic ABS-UV stabilised: decorative frame |
| Height | 110 mm |
| Width | 85 mm |
| Depth | 20 mm |
| Net Weight | 0.02 kg |
| Resistance To Chemical Agents | Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane |

Environment

| | |
|---------------------------------------|---|
| Ambient Air Temperature For Storage | -5...50 °C |
| Ambient Air Temperature For Operation | 5...45 °C |
| Standards | UNE 20315-1-1 EN 60669-1 NF C 61-314 2006/95/EEC |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|-------------------------|--|
| Product Certifications | AENOR: 030/2205 LCIE: NF 603415A N NF |
| Ik Degree Of Protection | IK04 |
| Ip Degree Of Protection | IP21D |

Packing Units

| | |
|------------------------------|----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 2.2 cm |
| Package 1 Width | 8.5 cm |
| Package 1 Length | 11.0 cm |
| Package 1 Weight | 20.0 g |
| Unit Type Of Package 2 | BB1 |
| Number Of Units In Package 2 | 2 |
| Package 2 Height | 4.8 cm |
| Package 2 Width | 10.7 cm |
| Package 2 Length | 16.6 cm |
| Package 2 Weight | 78.0 g |
| Unit Type Of Package 3 | S03 |
| Number Of Units In Package 3 | 56 |
| Package 3 Height | 30.0 cm |
| Package 3 Width | 30.0 cm |
| Package 3 Length | 40.0 cm |
| Package 3 Weight | 2.659 kg |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Sustainable Packaging Transparency RoHS/REACH

Resource performance

✓ Sustainable Packaging

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

| | |
|--------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |