

Product data sheet

Specifications



Orion roller blind switch 6A 250V, 2 modules, white

S70010804

Main

Range Of Product	Orion
Product Or Component Type	Switch
Device Presentation	Mechanism
Type Of Packing	Flow-pack
Quantity Per Set	Set of 20
Sale Per Indivisible Quantity	1
Colour Tint	White (RAL 9003)

Complementary

Device Mounting	Flush Surface
Switch Function	3 positions
Number Of Modules	1 module
Number Of Rocker	1
Actuator	Rocker
Switch Application	Shutter control
Range Compatibility	Orion shutter control OptiLine 70 adaptor plate
Fixing Mode	Clip-in
Marking	0 position Arrow
Surface Finish	Glossy
Surface Treatment	Untreated
Rated Current	6 A at 127/250 V AC 50/60 Hz
Connections - Terminals	Screwless terminals
Minimum Load Breaking Capacity	200 operations 1.25 In and 1.1 Un
Electrical Durability	2000 cycles conforming to IEC 60669
Connections - Terminals	6 screwless terminals
Shape Of Screw Head	Pozidriv No 2 Philips No 2
Clamping Connection Capacity	<= 2.5 mm² for rigid cable(s) <= 2.5 mm² for flexible cable(s)
Wire Stripping Length	11 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Material	CuZn15: terminals PC (polycarbonate) GF10 FR: casing Thermoplastic ABS-UV stabilised: mechanism rocker PBT (polybutylene terephthalate) GF30: release button
Height	45 mm
Width	45 mm
Depth	44.35 mm
Embedding Depth	32.8 mm
Net Weight	0.0335 kg

Environment

Ambient Air Temperature For Storage	-5...40 °C
Dielectric Strength	2000 V
Ambient Air Temperature For Operation	-5...35 °C
Standards	IEC 60669
Product Certifications	INMETRO
Ik Degree Of Protection	IK04
Ip Degree Of Protection	IP4X
Environmental Characteristic	Acetone Alcohol Bleach Liquid soap Hydrogen peroxide (H2O2) Oil Petrol UV resistant Window-cleaning fluid

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9 cm
Package 1 Width	14 cm
Package 1 Length	4.5 cm
Package 1 Weight	35 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	20
Package 2 Height	15.2 cm
Package 2 Width	16 cm
Package 2 Length	25.9 cm
Package 2 Weight	818 g