

Product data sheet

Specifications



Orion - two way switch 10AX 250V - 1 module - white

S70110304

Main

Range Of Product	Orion
Product Or Component Type	Switch
Device Presentation	Mechanism
Device Application	Lighting
Type Of Packing	Flow-pack
Quantity Per Set	Set of 20
Sale Per Indivisible Quantity	1

Complementary

Device Mounting	Flush
Switch Function	1-pole 2-way
Number Of Modules	1 module
Number Of Rocker	1
Actuator	Rocker
Range Compatibility	Orion fixing frame Orion adaptor plate OptiLine 70 with adaptor plate
Fixing Mode	Clip-in
Surface Finish	Glossy
Surface Treatment	Untreated
Rated Current	10 AX at 127/250 V AC 50/60 Hz
Minimum Load Breaking Capacity	200 operations 1.25 In and 1.1 Un
Electrical Durability	20000 cycles conforming to IEC 60669
Connections - Terminals	3 screw terminals
Shape Of Screw Head	Pozidriv No 2
Clamping Connection Capacity	<= 4 mm² for rigid cable(s) <= 4 mm² for stranded cable(s) <= 4 mm² for flexible cable(s)
Wire Stripping Length	11 mm
Local Signalling	LED optional

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Material	Thermoplastic ABS-UV stabilised: mechanism rocker PC (polycarbonate) GF10 FR: casing PC (polycarbonate) GF10 FR: cover Stainless steel: spring PA (polyamide) 66 GF25 FR: inner rocker Silver alloy: contact Brass: terminals Steel: nut Steel: screw
Height	45 mm
Width	22.5 mm
Depth	37 mm
Embedding Depth	25.1 mm
Net Weight	0.0226 kg

Environment

Ambient Air Temperature For Storage	-5...40 °C
Dielectric Strength	2000 V
Ambient Air Temperature For Operation	-5...35 °C
Standards	IEC 60669
Product Certifications	INMETRO NOM/ANCE INGCER
Ik Degree Of Protection	IK04
Ip Degree Of Protection	IP21D
Environmental Characteristic	Petrol UV resistant Alcohol Liquid soap Bleach Acetone Oil Window-cleaning fluid Hydrogen peroxide (H2O2)

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.3 cm
Package 1 Width	7.0 cm
Package 1 Length	14.0 cm
Package 1 Weight	24.0 g

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations